

PRECISION FLAT AND SQUARE BAR STEEL WITH MACHINING ALLOWANCE, DIN 59350

Material:

1.0570 / St 52-3

Non-alloyed construction steel


Execution:

Thickness precision ground, width ground or milled, length machined

2923.0570.



we deliver original
BÖHLER
quality



2923.0570. Precision flat and square bar steel with machining allowance, DIN 59350

s	5.2	6.2	8.2	10.4	12.4	15.4	20.4	25.4	30.4	40.4	50.4	60.4	70.4	80.4	100.4
b															
10.4				●											
12.4					●										
15.4						●									
20.3		●	●	●	●	●									
20.4							●								
25.3	●	●	●	●	●	●	●								
25.4								●							
30.3	●	●	●	●	●	●	●	●							
30.4									●						
40.3	●	●	●	●	●	●	●	●	●						
40.4										●					
50.3	●	●	●	●	●	●	●	●	●	●					
50.4											●				
60.3	●	●	●	●	●	●	●	●	●	●	●				
60.4												●			
70.3				●	●	●	●	●	●	●	●	●			
70.4													●		
80.3	●	●	●	●	●	●	●	●	●	●	●	●	●		
80.4														●	
100.3	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
100.4															●
120.3			●	●	●	●	●	●	●	●	●	●	●	●	●
125.3	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
140.3			●	●	●	●	●	●	●	●	●	●	●	●	●
150.3	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
160.3	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
180.3			●	●	●	●	●	●	●	●	●	●	●	●	●
200.3		●	●	●	●	●	●	●	●	●	●	●	●	●	●
250.3		●	●	●	●	●	●	●	●	●	●	●	●	●	●
300.3			●	●	●	●	●	●	●	●	●	●	●	●	●
350.3			●	●	●	●	●	●	●	●	●	●	●	●	●
400.3			●	●	●	●	●	●	●	●	●	●	●	●	●

Ordering Code (example):

Precision flat and square bar steel with machining allowance, DIN 59350	=	2923.0570.
Width B	50.3 mm =	050.
Thickness S	5.2 mm =	005.
Length L	1000 mm =	1000
Order No	=	2923.0570. 050. 005. 1000