

DIE LIFTING BOLT WITH SAFETY RING AND SPRING, CNOMO STANDARD

2132.11.





Mounting example



Note:

It is important to ensure that there is safety clearance on both outer sides of the cast cheeks and that there is room for installation on one side. The lifting bolt must always be introduced from the outside of the tool towards the middle.

2132.11. Die lifting bolt with safety ring and spring, CNOMO Standard

max. carrying capacity (2 lifting flanges) [kg]* 12,000 Order No 2132.11.032 12 154 132 40 32 22 25 10 2132.11.040 2132.11.050 2132.11.063 18,000 50 40 28 16 197.75 170 12.5 13.75 28,000

^{*}The maximum permissible load capacity is to be calculated such that two bolts on their own are capable of carrying or turning the tool.