

# PRECISION FLAT AND SQUARE BAR STEEL WITH MACHINING ALLOWANCE, DIN 59350

2923.2099.




**Material:**

1.2099 / X5 CrS 12  
Stainless steel for plastic moulding,  
tempered to 900-1050 N/mm<sup>2</sup>

**Execution:**

Thickness precision ground, width ground or milled,  
length machined



**2923.2099. Precision flat and square bar steel with machining allowance, DIN 59350**

s	6.2	8.2	10.4	15.4	20.4	25.4	30.4	40.4	50.4
b									
20.3	●	●	●						
25.3	●	●	●	●					
30.3	●	●	●	●	●				
40.3	●	●	●	●	●	●			
50.3	●	●	●	●	●	●	●		
60.3	●	●	●	●	●	●	●	●	
80.3	●	●	●	●	●	●	●	●	●
100.3	●	●	●	●	●	●	●	●	●
125.3	●	●	●	●	●	●	●	●	●
150.3	●	●	●	●	●	●	●	●	●
200.3	●	●	●	●	●	●	●	●	●
250.3	●	●	●	●	●	●	●	●	●
300.3	●	●	●	●	●	●	●	●	●

**Ordering Code (example):**

Precision flat and square bar steel with machining allowance, DIN 59350	=	2923.2099.
Width B	80.3 mm =	080.
Thickness S	6.2 mm =	006.
Length L	500 mm =	0500
Order No	=	2923.2099. 080. 006. 0500