



ELASTOMER STRIPPER



Mounting example



243.7.



Description:

Repairs, sharpening and modifications on dies equipped with elastomer strippers do not necessitate the dismantling of a stripper plate, thus becoming very expedient. Any marring of delicate part surfaces is precluded. This makes elastomer strippers ideal for all painted, anodized, plastic-coated and polished parts. FIBROFLEX® Elastomer Strippers are resistant against oils and greases.

Material:

FIBROFLEX®
Hardness: 95 Shore A

Execution:

Stock lengths: 39, 47, 56 mm.
Other lengths on request (max. 56 mm)!

Application:

Especially in large dies, where the use of elastomer strippers does away with the need of huge stripper plates.

Mounting:

Push stripper over punch, where it will stay put on account of its elasticity. No other form of retention will be required. A single press stroke will then pierce a hole through the bottom portion of the stripper that matches the punch shape exactly.

243.7. Elastomer Stripper

d ₁	d ₂	d ₃	L ₀	39	47	56
4	17	1.6		●	●	●
5	17	1.6		●	●	●
6	19	1.6		●	●	●
6.3	19	1.6		●	●	●
8	21	3		●	●	●
10	23	3		●	●	●
12.5	26	3		●	●	●
13	26	3		●	●	●
16	30	3		●	●	●
20	38	3		●	●	●
25	50	3		●	●	●
32	55	3		●	●	●
38	60	3		●	●	●
40	63	3		●	●	●

Ordering Code (example):

Elastomer Stripper	=	243.7.
Inner diameter d ₁	13 mm =	130.
Length L ₀	39 mm =	039
Order No	=	243.7. 130.039